



FEATURES

- VariColour filter blocked warning system
- Highest grade HEPA and carbon technology
- Automatic electronic flow control - maintains a constant extraction rate even as the filter blocks
- Quiet in operation
- Simple to install and easy to relocate


Specifications

Voltage	90v - 254v
Part Number	0EL4110
Wattage	1.1kW
Frequency	50Hz / 60Hz
Cabinet Height	715mm
Cabinet Width	975mm
Cabinet Depth	700mm
Cabinet Weight	70Kg
Sound Level	<60dBa
Airflow	350m3/h

Find out more:

-  www.jorlink.com
-  sales@fumefiltration.com
- sales@jorlink.com
-  (336) 288-1613

Filters



Main Filter Code 110553
Description HEPA



Main Filter Code 110548
Description Carbon



Pre-filter Code 111118
Description F8/F9 Labyrinth



Pre-filter Code 111114
Description Cascade

**Connection kit is included
 see overleaf for options**


Connection Kits

Hose End Diameter


Hose Length

Purex Inlet Diameter


Code: 100107 **100mm** **3m** **100mm**




Code: 100105 **100mm** **2m** **100mm**




Code: 120270 **100mm** **1.5m** **100mm**




Code: 120292 **80mm** **1.3m** **100mm**



Code: 100194 **50mm** **2.5m** **100mm**




Code: 100193 **50mm** **3.5m** **100mm**



If you do not see a connection kit that fits your machine or pipework, please contact Purex or your representative

Interfacing



Interfacing can remotely start the Purex machine when the connected machine starts.

Interfacing can also warn the connected machine when the Purex machine is in alarm.

Take a look through our Interfacing Guide to see our extensive range of options



T. 336-288-1613 eMail: Sales@fumefiltration.com

Jorlink USA, Inc, 3714 Alliance Dr.,
Suite 100
Greensboro, NC 27407
sales@jorlink.com
sales@fumefiltration.com
Tel (336) 288-1613